





Maintenance	
Ergonomics:	The Rekola Addon pouch reduces the trafficking, as it influences the process of walking back and forward to the cleaning trolley during the daily manual cleaning.
Cleaning:	The EVA pouches are -20° and +100° Celsius and disinfectant chemicals resistant. Rinse the bag with hot water and optional disinfect with disinfecting liquid. Do not use Deko-machines as the temperature change may deform the shape of the pouch.
Disposable:	EVA and stainless steel when collected separately can be recycled.
Components	
Pouch	EVA (Ethylene Vinyl Acetate), 18-20% VA pouch.
Velcro and hook	Polyester Velcro on top and on bottom. Stainless steel hook on top for hanging.
Characteristics	
functionality	Rekola Addon EVA pouches offer a flexible way of personalizing your cleaning trolley and cleaning process. Because the pouches are multifunctional there are almost no limitations for usage within the cleaning process.
ergonomics	As the Rekola Addon EVA pouches are extremely light, the carrier can comfortably bring the bag from the trolley to the laundry. During cleaning activity the pouch can be hung on the side on the doorknob, separation walls or coat-hooks.
Guarantee	
One year manufacturer guarantee after purchase.	